

CAPILLARY ADAPTOR

(ABS009/27 - 27mm)



Used when a 27mm connection is required to 10mm OD nylon tubing. To create a trunk adaptor or a capillary end cap.

Installation Instructions:

Use the correct solvent Plusbond 3019. Do not paint. Keep pipe clean and free from dust. Do not install in direct sunlight. Only install with approved pipe. Do not use solvents to clean, only soapy water.

OPERATING
TEMPERATURE:
-40°C to 70°C

PIPE COLOUR: Red

DIAMETER TOLERANCE:
+/- 0.15mm

