CAPILLARY ADAPTOR

(ABSG009/25 - 25mm)



Used when a 25mm connection is required to 10mm OD nylon tubing. To create a trunk adaptor or a capillary end cap.

Installation Instructions:

Use the correct solvent Plusbond 3019. Do not paint. Keep pipe clean and free from dust. Do not install in direct sunlight. Only install with approved pipe. Do not use solvents to clean, only soapy water.

OPERATING TEMPERATURE: -40°C to 70°C PIPE COLOUR: Grey

DIAMETER TOLERANCE:

+/- 0.15mm













