

NYLON TUBING

(WHABS018/25)



To join the trunk adapter to the sampling head of choice: Flush, Conical or Discrete.
Available in 30 or 100 meters lengths.

Installation Instructions:

Push fit into both the trunk adapter and the sampling head. Do not paint. Keep pipe clean and free from dust. Do not install in direct sunlight. Only install with approved pipe. Do not use solvents to clean, only soapy water.

PIPE COLOUR:
White

DIAMETER TOLERANCE:
+/- 0.15mm

DIMENSIONS:
10mm OD
8mm ID

MATERIAL:
Nylon

