## DISCRETE KIT WITH TEE COMPRESSION ADAPTOR



(ABS042D - 25mm)

Used mainly in office blocks, the socket compression adapter offers a simple way of attaching the 10mm tubing to the 25mm pipe, by simply clicking it into place and removing it by pressing down on the black ring.

## Installation Instructions:

Use the correct solvent Plusbond 3019. Do not paint. Keep pipe clean and free from dust. Do not install in direct sunlight. Only install with approved pipe. Do not use solvents to clean, only soapy water.

